

IE-FSMZ2LY0005MST0ST0-X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5, 6 and 14
- consistently Cat. 6A with STEADYTEC® technology
- in IP20 and IP67
- all relevant industrial connections: RJ45, SC, ...
- comprehensive range of accessories

General ordering data

Version	Pre-assembled patch cable, crossover, ST IP 20, ST IP 20, 9 µm, LSZH, 5 m
Order No.	2703930050
Type	IE-FSMZ2LY0005MST0ST0-X
GTIN (EAN)	4050118733143
Qty.	1 items

IE-FSMZ2LY0005MST0ST0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Length	5 m	Length (inches)	196.8504 inch
Net weight	0.01 g		

Temperatures

Storage temperature	-25 °C...75 °C	Operating temperature	-5 °C...75 °C
Installation temperature	-5 °C...50 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Fibre-optic

Fibre type Singlemode, OS1

Cable structure

Sheath diameter	3*6 mm	Sheathing colour	yellow
Standard designations	I-V(ZN)Y	Material sheath	LSZH
Cable layout	ZIPCORD	Primary coating	245.00 µm
Core diameter	9 µm		

Classifications

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		