

TS TTB 6 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

General ordering data

Version	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
Order No.	2710520000
Type	TS TTB 6 BK
GTIN (EAN)	4050118881080
Qty.	48 items

TS TTB 6 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	51.3 mm	Depth (inches)	2.0197 inch
Height	9.4 mm	Height (inches)	0.3701 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	1.1 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	black
UL 94 flammability rating	V-0		

Additional technical data

Type of fixing	Plugged	Explosion-tested version	No
Type of mounting	Plug		

Dimensions

Plug-in depth	11.5 mm
---------------	---------

General

Operating temperature range, max.	130 °C
-----------------------------------	--------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		



