

**TS TTB 6 VT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

**General ordering data**

Version	Socket (terminal), Plug-in depth: 11.5 mm, 0.00 mm, Depth: 51.3 mm
Order No.	<a href="#">2710530000</a>
Type	TS TTB 6 VT
GTIN (EAN)	4050118881097
Qty.	48 items

**TS TTB 6 VT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	51.3 mm	Depth (inches)	2.0197 inch
Height	9.4 mm	Height (inches)	0.3701 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	1.1 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Wemid	Colour	violet
UL 94 flammability rating	V-0		

**Additional technical data**

Type of fixing	Plugged	Explosion-tested version	No
Type of mounting	Plug		

**Dimensions**

Metric size of the thread, external	0.00 mm	Plug-in depth	11.5 mm
-------------------------------------	---------	---------------	---------

**General**

Operating temperature range, max.	130 °C
-----------------------------------	--------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		



