


THM WO-QX VIN 25/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

| | |
|------------|--|
| Version | THM, Conductor and cable markers, 12.2 - 24.4 mm, 25 x 100 mm, white |
| Order No. | 2711970000 |
| Type | THM WO-QX VIN 25/100 WS |
| GTIN (EAN) | 4050118749960 |
| Qty. | 1000 items |

THM WO-QX VIN 25/100 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.08 mm | Depth (inches) | 0.0031 inch |
| Height | 25 mm | Height (inches) | 0.9842 inch |
| Width | 100 mm | Width (inches) | 3.937 inch |
| Net weight | 0.59 g | | |

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--------------------------------------|--|------------|--|
| Adhesive | Polyacrylate adhesive | | |
| Orientation of print | horizontal and vertical | | |
| Type of printing | neutral | | |
| Width | 100 mm | | |
| UL 94 flammability rating | V-0 | | |
| Operating temperature range, max. | 80 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | white | | |
| Halogen | Yes | | |
| Basic material | Vinyl film | | |
| Printed characters | without | | |
| Number of markers per packaging unit | Form of supply | Label reel | |
| Approval acc. to UL 969 | Yes | | |
| compatible printer | THM MULTIMARK , THM MULTIMARK PLUS | | |
| Number of markers per combination | 1 Label reel = Conductor and cable markers | | |
| Operating temperature range | -40...80 °C | | |
| Number per roll | 1000 | | |


Conductor and cable markers

| | | | |
|----------------------|----------------|----------------------------------|---------------------|
| Halogen | Yes | Conductor cross-section, max. | 467 mm ² |
| Conductor O.D., max. | 24.4 mm | Conductor O.D., min. | 12.2 mm |
| Conductor O.D. | 12.2 - 24.4 mm | Cross-section for connected wire | 467 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings



THM WO-QX VIN 25/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM 76/360 SW | Version | |
| Order No. | 2005080000 | Ink ribbon | |
| GTIN (EAN) | 4050118389951 | | |
| Qty. | 1 ST | | |
| Type | RIBBON MM 110/360 SW | Version | |
| Order No. | 2005070000 | Ink ribbon | |
| GTIN (EAN) | 4050118390049 | | |
| Qty. | 1 ST | | |