

MF 10/6 MM BP WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MultiMark MultiFit

For connectors from competitors.

The elastic surface finish makes for simple installation.

This special material enables the strips to be stretched to accommodate slight variations in spacing, especially with long terminal blocks.

A print resolution of 300 dpi also produces a very legible script. Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
-] • Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

Version	Terminal marker, 10 x 6 mm, white
Order No.	2712160000
Type	MF 10/6 MM BP WS
GTIN (EAN)	4050118749472
Qty.	3800 items

MF 10/6 MM BP WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.7 mm	Depth (inches)	0.0276 inch
Height	10 mm	Height (inches)	0.3937 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	0.12 g		

Temperatures

Operating temperature range	-50...90 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	halogen-free	Width	6 mm
UL 94 flammability rating	V-2	Operating temperature range, max.	90 °C
Operating temperature range, min.	-50 °C	Colour	white
Halogen	No	Basic material	PC-ABS, TPU
Printed characters	neutral	compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Operating temperature range	-50...90 °C		

Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Drawings



MF 10/6 MM BP WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-TB 25/360 SW	Version	
Order No.	2005090000	Ink ribbon	
GTIN (EAN)	4050118390216		
Qty.	1 ST		

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP EXT.RH	Version	
Order No.	1302920000		
GTIN (EAN)	4050118102307		
Qty.	1 ST		