

**CH-HMBC-HMBD-08-0100-AD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The increasingly networked industrial world goes hand in hand with the modularization of machines and systems. Functions from the control cabinet are increasingly being moved to field level, which drives up the amount of cabling required.

Our ready-for-connection cable assemblies can be used wiring in field level and for transmitting data or power in various applications. The Plug & Produce solution by Weidmüller are fully tested and will lead to simplification of assembly on your machine. This allows you to focus on your core competencies and further increase your efficiency.

With our broad product portfolio of certified components, we offer you a wide diversification so that we can provide you the perfect solution for your application.

If you cannot find the cable assembly you are looking for despite our continuously growing portfolio, we can also offer you different length variants and customer-specific solutions.

**General ordering data**

|                 |                                                                                                                                       |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Version         | Heavy duty connector assemblies, Pin, Socket connector, Helukabel MEGAFLEX 500-C 10G2.5 or similar, Shielded: Yes, Number of poles: 8 |
| Order No.       | <a href="#">2712460100</a>                                                                                                            |
| Type            | CH-HMBC-HMBD-08-0100-AD                                                                                                               |
| GTIN (EAN)      | 4050118779578                                                                                                                         |
| Qty.            | 1 items                                                                                                                               |
| Delivery status | Discontinued                                                                                                                          |

## CH-HMBC-HMBD-08-0100-AD

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |          |
|------------|----------|
| Net weight | 890.22 g |
|------------|----------|

## Temperatures

|                   |                  |
|-------------------|------------------|
| Limit temperature | -40 °C ... 80 °C |
|-------------------|------------------|

## Environmental Product Compliance

|                                      |                                                                                                                       |
|--------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| RoHS Compliance Status               | Compliant with exemption                                                                                              |
| RoHS Exemption (if applicable/known) | 6c                                                                                                                    |
| REACH SVHC                           | Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1 |
| SCIP                                 | 1344e4a2-b558-4ad0-95d1-5c6df3fdd75e                                                                                  |

## General Technical Data

|                 |       |                   |                     |
|-----------------|-------|-------------------|---------------------|
| Number of poles | 8     | Pin arrangement   | 1:1, numbered cores |
| Nominal voltage | 500 V | Protection degree | IP65                |

## Technical Specifications Connector

|           |                                 |                                                                                                                                            |
|-----------|---------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Connector | Connector description           | Connector 1                                                                                                                                |
|           | Cable entry                     | straight                                                                                                                                   |
|           | Housing main material           | Zinc diecast                                                                                                                               |
|           | Number of poles                 | 8                                                                                                                                          |
|           | Series                          | HQ                                                                                                                                         |
|           | Size                            | HQ                                                                                                                                         |
|           | Type                            | Pin                                                                                                                                        |
|           | Individual components connector | <a href="#">HDC HQM TOLU 1PG21</a> , <a href="#">HDC HQ 8 MC</a> , <a href="#">HDC-C-HE-SM2.5AG</a> , <a href="#">VG 21 HQ EMV68 14-18</a> |
|           | Connector description           | Connector 2                                                                                                                                |
|           | Cable entry                     | straight                                                                                                                                   |
|           | Housing main material           | Zinc diecast                                                                                                                               |
|           | Number of poles                 | 8                                                                                                                                          |
|           | Series                          | HQ                                                                                                                                         |
|           | Size                            | HQ                                                                                                                                         |
|           | Type                            | Female                                                                                                                                     |
|           | Individual components connector | <a href="#">HDC HQM TOLU 1PG21</a> , <a href="#">HDC HQ 8 FC</a> , <a href="#">HDC-C-HE-BM2.5AG</a> , <a href="#">VG 21 HQ EMV68 14-18</a> |

## Technical specifications for cable

|                                     |                      |                                     |                                            |
|-------------------------------------|----------------------|-------------------------------------|--------------------------------------------|
| Cable length                        | 1 m                  | Line type                           | Helukabel MEGAFLEX 500-C 10G2.5 or similar |
| Sheathing colour                    | grey                 | Core cross-section                  | 2.5 mm <sup>2</sup>                        |
| Number of wires                     | 10                   | Shielded                            | Yes                                        |
| Halogen                             | No                   | Insulation                          | Halogen Free Polymer                       |
| Temperature range, moving, max.     | 80 °C                | Temperature range, moving, min.     | -30 °C                                     |
| Temperature range, stationary, max. | 80 °C                | Temperature range, stationary, min. | -40 °C                                     |
| Bending radius, min., moving        | 10 x cable diameter  | Bending radius, min., stationary    | 4 x cable diameter                         |
| Sheath material                     | Halogen Free Polymer | Outside diameter                    | 14 mm                                      |

**Technical data****Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001576    | ETIM 9.0    | EC001576    |
| ETIM 10.0   | EC001576    | ECLASS 14.0 | 27-06-04-02 |
| ECLASS 15.0 | 27-06-04-02 |             |             |

## CH-HMBC-HMBD-08-0100-AD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## 8-pole



A small size but quite big. The electrical values speak for themselves. Proven HE crimp contacts can also be used here.

Pole count: 8 (+PE)

Rated current: 16 A

Rated voltage: 500 V

Nominal voltage acc. to UL/CSA: 600 V AC/DC

## General ordering data

|            |                            |                                                                                              |
|------------|----------------------------|----------------------------------------------------------------------------------------------|
| Type       | HDC HQ 8 MC                | Version                                                                                      |
| Order No.  | <a href="#">1919970000</a> | HDC insert, Male, 500 V, 16 A, Number of poles: 8, Crimp connection, Installation size: HQ   |
| GTIN (EAN) | 4032248557943              |                                                                                              |
| Qty.       | 1 ST                       |                                                                                              |
| Type       | HDC HQ 8 FC                | Version                                                                                      |
| Order No.  | <a href="#">1919980000</a> | HDC insert, Female, 500 V, 16 A, Number of poles: 8, Crimp connection, Installation size: HQ |
| GTIN (EAN) | 4032248557950              |                                                                                              |
| Qty.       | 1 ST                       |                                                                                              |

## Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

## General ordering data

|            |                            |                                                                                                                                                                                 |
|------------|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type       | HDC HQP ALU                | Version                                                                                                                                                                         |
| Order No.  | <a href="#">1003040000</a> | HDC enclosures, Installation size: HQ, Protection degree: IP65, in plugged condition, Bulkhead housing, Side-locking clamp on lower side, Standard, Size of cable entries: none |
| GTIN (EAN) | 4032248697977              |                                                                                                                                                                                 |
| Qty.       | 1 ST                       |                                                                                                                                                                                 |

## CH-HMBC-HMBD-08-0100-AD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Angled bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

## General ordering data

| Type       | HDC HQP AWLU               | Version                                                            |
|------------|----------------------------|--------------------------------------------------------------------|
| Order No.  | <a href="#">1003060000</a> | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4032248697991              | plugged condition, Bulkhead housing, Side-locking clamp on lower   |
| Qty.       | 1 ST                       | side, Standard, Size of cable entries: none                        |

## Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

## General ordering data

| Type       | HDC HQP ALU CS             | Version                                                            |
|------------|----------------------------|--------------------------------------------------------------------|
| Order No.  | <a href="#">1354950000</a> | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4050118157215              | plugged condition, Bulkhead housing, Side-locking clamp on lower   |
| Qty.       | 1 ST                       | side, Standard, Size of cable entries: none                        |

## CH-HMBC-HMBD-08-0100-AD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Coupling housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | HDC HQP KOLU 1PG16         | Version                                                            |
| Order No.  | <a href="#">1003120000</a> | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4032248698059              | plugged condition, Coupling housing, Side-locking clamp on lower   |
| Qty.       | 1 ST                       | side, Standard, Size of cable entries: PG 16                       |

## Base housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | HDC HQP SLU 1PG16          | Version                                                            |
| Order No.  | <a href="#">1003110000</a> | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4032248698042              | plugged condition, Base housing, Side-locking clamp on lower side, |
| Qty.       | 1 ST                       | Standard, Size of cable entries: PG 16                             |

## CH-HMBC-HMBD-08-0100-AD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | HDC HQM ALU                | Version                                                            |
| Order No.  | <a href="#">1003050000</a> | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4032248697984              | plugged condition, Bulkhead housing, Side-locking clamp on lower   |
| Qty.       | 1 ST                       | side, Standard, Size of cable entries: none                        |
| Type       | HDC HQM ALU CS             | Version                                                            |
| Order No.  | <a href="#">1251680000</a> | HDC enclosures, Installation size: HQ, Protection degree: IP65, in |
| GTIN (EAN) | 4050118051803              | plugged condition, Bulkhead housing, Side-locking clamp on lower   |
| Qty.       | 1 ST                       | side, Standard, Size of cable entries: none                        |