

HDC XX6A02 O0XXXDM-1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Order No.	2712681000
Type	HDC XX6A02 O0XXXDM-1000
GTIN (EAN)	4050118753028
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-30T00:00:00+02:00

HDC XX6A02 OOXXXDM-1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	10 m	Length (inches)	393.7008 inch
Net weight	2300 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Number of poles	8	Cable length	100 m
Insulation resistance	$\geq 500 \text{ M}\Omega$	Category	Cat. 7 (ISO/IEC 11801)
Nominal voltage	100 V	Nominal current	0.5 A
Pollution severity	2	Opposite side version	open
Module side version	open		

Cable technical specifications

Cable length	100 m	Sheathing colour	green
Halogen	halogen-free, according to IEC 60754-1	Insulation	PE
Sheath material	PUR		

Classifications

ETIM 8.0	EC003249	ETIM 9.0	EC003249
ETIM 10.0	EC003249	ECLASS 14.0	27-06-18-01
ECLASS 15.0	27-06-18-01		