

PRINTJET CONNECT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The PrintJet CONNECT is the consistent further development of our tried-and-tested PrintJet series. Focusing on the modern needs of industry and panel building, it combines maximum process and cost efficiency with intelligent networking and complete data consistency. For example, you can use existing data directly in the marking process – for working more efficiently and with a minimal error rate.

General ordering data

Version	Marking systems, Ink jet technology, 1200 DPI, Multicard, MetalliCard
Order No.	2715590000
Type	PRINTJET CONNECT
GTIN (EAN)	4064675016922
Qty.	1 items

PRINTJET CONNECT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	930 mm	Depth (inches)	36.6141 inch
Height	454 mm	Height (inches)	17.874 inch
Width	590 mm	Width (inches)	23.2283 inch
Net weight	43693 g		

Temperatures

Ambient temperature 18 °C...32 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6aI, 6c, 7a, 7cI, 34
REACH SVHC	Lead 7439-92-1, Hexahydromethylphthalic anhydride 19438-60-9, Cyclohexane-1,2-dicarboxylic anhydride 85-42-7, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1, 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol 79-94-7
SCIP	1019ebc1-7078-40d9-974d-3aa332713b10

Labelling systems

Marker type	Multicard, MetalliCard	Fueling system	Ink cartridge, CMYK
Printing method	Ink jet technology	Interface	USB, LAN, Wi-Fi
Software	M-Print® PRO	Supply voltage	230 V AC / 16 A, 115 V AC / 20 A
Operating system	Windows 8, Windows 8.1, Windows 10, Windows 11	Printer driver	Windows 8, Windows 8.1, Windows 10, Windows 11
Printing speed	Depends on printing quality	Print resolution, max.	1200 DPI
Included in delivery	PrintJet CONNECT, Power cable, USB cable, 1 unit DEK 5/5, 2 x PrintJet Cleaner tissues, Quick start guide, Dust cover, 1 set of ink cartridges CMYK		

Classifications

ETIM 8.0	EC000610	ETIM 9.0	EC000610
ETIM 10.0	EC000610	ECLASS 14.0	24-32-11-90
ECLASS 15.0	24-32-11-90		