

**PRINTJET CONNECT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The PrintJet CONNECT is the consistent further development of our tried-and-tested PrintJet series. Focusing on the modern needs of industry and panel building, it combines maximum process and cost efficiency with intelligent networking and complete data consistency. For example, you can use existing data directly in the marking process – for working more efficiently and with a minimal error rate.

**General ordering data**

|            |   |
|------------|---|
| Version    | Marking systems, Ink jet technology, 1200 DPI, Multicard, MetalliCard |
| Order No.  | <a href="#">2715590000</a>  |
| Type       | PRINTJET CONNECT  |
| GTIN (EAN) | 4064675016922   |
| Qty.       | 1 items   |

**PRINTJET CONNECT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

|            |         |                 |              |
|------------|---------|-----------------|--------------|
| Depth      | 930 mm  | Depth (inches)  | 36.6141 inch |
| Height     | 454 mm  | Height (inches) | 17.874 inch  |
| Width      | 590 mm  | Width (inches)  | 23.2283 inch |
| Net weight | 43693 g |                 |              |

**Temperatures**

Ambient temperature 18 °C...32 °C

**Environmental Product Compliance**

|                                      |   |
|--------------------------------------|---|
| RoHS Compliance Status               | Compliant with exemption  |
| RoHS Exemption (if applicable/known) | 6aI, 6c, 7a, 7cl, 34  |
| REACH SVHC                           | Lead 7439-92-1, Hexahydromethylphthalic anhydride 19438-60-9, Cyclohexane-1,2-dicarboxylic anhydride 85-42-7, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1, 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol 79-94-7 |
| SCIP                                 | 1019ebc1-7078-40d9-974d-3aa332713b10  |

**Labelling systems**

|                      |   |                        |  |
|----------------------|---|------------------------|--|
| Marker type          | Multicard, MetalliCard  | Fueling system         | Ink cartridge, CMYK                            |
| Printing method      | Ink jet technology  | Interface              | USB, LAN, Wi-Fi                                |
| Software             | M-Print® PRO  | Supply voltage         | 230 V AC / 16 A, 115 V AC / 20 A               |
| Operating system     | Windows 8, Windows 8.1, Windows 10, Windows 11  | Printer driver         | Windows 8, Windows 8.1, Windows 10, Windows 11 |
| Printing speed       | Depends on printing quality   | Print resolution, max. | 1200 DPI                                       |
| Included in delivery | PrintJet CONNECT, Power cable, USB cable, 1 unit DEK 5/5, 2 x PrintJet Cleaner tissues, Quick start guide, Dust cover, 1 set of ink cartridges CMYK |                        |  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000610    | ETIM 9.0    | EC000610    |
| ETIM 10.0   | EC000610    | ECLASS 14.0 | 24-32-11-90 |
| ECLASS 15.0 | 24-32-11-90 |             |             |

## PRINTJET CONNECT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### PrintJet CONNECT

Accessories and consumables for the PrintJet CONNECT



#### General ordering data

|            |                            |         |
|------------|----------------------------|---------|
| Type       | PJ CON CLEANING UNIT       | Version |
| Order No.  | <a href="#">2715700000</a> |         |
| GTIN (EAN) | 4064675042099              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON FLUID SET           | Version |
| Order No.  | <a href="#">2715650000</a> |         |
| GTIN (EAN) | 4064675036036              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON INK C               | Version |
| Order No.  | <a href="#">2715610000</a> |         |
| GTIN (EAN) | 4064675041573              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON INK K               | Version |
| Order No.  | <a href="#">2715640000</a> |         |
| GTIN (EAN) | 4064675041887              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON INK M               | Version |
| Order No.  | <a href="#">2715620000</a> |         |
| GTIN (EAN) | 4064675042044              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON INK Y               | Version |
| Order No.  | <a href="#">2715630000</a> |         |
| GTIN (EAN) | 4064675041580              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON INK SET             | Version |
| Order No.  | <a href="#">2715600000</a> |         |
| GTIN (EAN) | 4064675041566              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON SERVICE FLAP        | Version |
| Order No.  | <a href="#">2715690000</a> |         |
| GTIN (EAN) | 4064675042082              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON TEXTILE COVER       | Version |
| Order No.  | <a href="#">2715670000</a> |         |
| GTIN (EAN) | 4064675042068              |         |
| Qty.       | 1 ST                       |         |
| Type       | PJ CON WASTE PAD           | Version |
| Order No.  | <a href="#">2715660000</a> |         |
| GTIN (EAN) | 4064675042051              |         |
| Qty.       | 1 ST                       |         |

## PRINTJET CONNECT

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### M-Print® PRO



The M-Print® PRO printing and ordering software for markers and labels® is a professional Windows®-based solution for both printing and ordering Weidmüller labels and markers . This software allows you to optimise the process of identifying electrical equipment. You can design and order your marking materials easily, professionally and quickly: with text, frames, lines, graphics, bar codes, serial numbers and photos.

- Integrated product catalogue for all labels and markers, incl. images, link to the website and product data sheet
- Markers and labels can be designed on as many levels as required
- Customised formatting of individual text characters (RTF)
- Copy and paste texts and their formats
- Available in 20 languages supporting UNICODE
- Data entry in labels and spreadsheets, or directly in Microsoft Excel
- Creation of scales; numeric and alpha-numeric counters and sequences
- Extensive range of image formats (\*.bmp, \*.wmf, \*.png, \*.ico, \*.jpeg, \*.jpg, \*.tif, \*.gif)
- Image library including symbols used in electrical engineering
- Product-printer allocation options, e.g. ESG 9/20 to PrintJet; MultiMark on thermotransfer printer
- Online update service via the Internet
- Weidmueller Configurator (WMC) interface
- Import wizard for a number of file formats (\*.txt, \*.csv, \*.xml, etc.) for creating your own import scripts
- Transfer of data from CAE systems
- Permanent print preview: see what the printout will look like even at the design phase, WYSIWYG editing
- Supported output devices: All Weidmueller printers (e.g. PrintJet CONNECT, THM MultiMark, etc.) and standard printers with Microsoft Windows® driver
- Optimal and fast adaptation of output devices
- Multi-level structuring of markers and labels

### General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | M-PRINT PRO                | Version  |
| Order No.  | <a href="#">1905490000</a> | Software for markings, Software, Windows 10, Windows 11, Printer |
| GTIN (EAN) | 4032248526291              | software   |
| Qty.       | 1 ST                       |  |