

**PRINTJET CONNECT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The PrintJet CONNECT is the consistent further development of our tried-and-tested PrintJet series. Focusing on the modern needs of industry and panel building, it combines maximum process and cost efficiency with intelligent networking and complete data consistency. For example, you can use existing data directly in the marking process – for working more efficiently and with a minimal error rate.

**General ordering data**

Version	Marking systems, Ink jet technology, 1200 DPI, Multicard, MetalliCard
Order No.	<a href="#">2715590000</a>
Type	PRINTJET CONNECT
GTIN (EAN)	4064675016922
Qty.	1 items

**PRINTJET CONNECT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	930 mm	Depth (inches)	36.6141 inch
Height	454 mm	Height (inches)	17.874 inch
Width	590 mm	Width (inches)	23.2283 inch
Net weight	43693 g		

**Temperatures**

Ambient temperature 18 °C...32 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6aI, 6c, 7a, 7cI, 34
REACH SVHC	Lead 7439-92-1, Hexahydromethylphthalic anhydride 19438-60-9, Cyclohexane-1,2-dicarboxylic anhydride 85-42-7, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1, 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol 79-94-7
SCIP	1019ebc1-7078-40d9-974d-3aa332713b10

**Labelling systems**

Marker type	Multicard, MetalliCard	Fueling system	Ink cartridge, CMYK
Printing method	Ink jet technology	Interface	USB, LAN, Wi-Fi
Software	M-Print® PRO	Supply voltage	230 V AC / 16 A, 115 V AC / 20 A
Operating system	Windows 8, Windows 8.1, Windows 10, Windows 11	Printer driver	Windows 8, Windows 8.1, Windows 10, Windows 11
Printing speed	Depends on printing quality	Print resolution, max.	1200 DPI
Included in delivery	PrintJet CONNECT, Power cable, USB cable, W-LAN stick, 1 unit DEK 5/5, 2 x PrintJet Cleaner tissues, Quick start guide, all other 23 languages on DVD as a PDF, Dust cover, 1 set of ink cartridges CMYK		

**Classifications**

ETIM 8.0	EC000610	ETIM 9.0	EC000610
ETIM 10.0	EC000610	ECLASS 14.0	24-32-11-90
ECLASS 15.0	24-32-11-90		

## PRINTJET CONNECT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### PrintJet CONNECT

Accessories and consumables for the PrintJet CONNECT



#### General ordering data

Type	PJ CON CLEANING UNIT	Version
Order No.	<a href="#">2715700000</a>	
GTIN (EAN)	4064675042099	
Qty.	1 ST	
Type	PJ CON FLUID SET	Version
Order No.	<a href="#">2715650000</a>	
GTIN (EAN)	4064675036036	
Qty.	1 ST	
Type	PJ CON INK C	Version
Order No.	<a href="#">2715610000</a>	
GTIN (EAN)	4064675041573	
Qty.	1 ST	
Type	PJ CON INK K	Version
Order No.	<a href="#">2715640000</a>	
GTIN (EAN)	4064675041887	
Qty.	1 ST	
Type	PJ CON INK M	Version
Order No.	<a href="#">2715620000</a>	
GTIN (EAN)	4064675042044	
Qty.	1 ST	
Type	PJ CON INK Y	Version
Order No.	<a href="#">2715630000</a>	
GTIN (EAN)	4064675041580	
Qty.	1 ST	
Type	PJ CON INK SET	Version
Order No.	<a href="#">2715600000</a>	
GTIN (EAN)	4064675041566	
Qty.	1 ST	
Type	PJ CON SERVICE FLAP	Version
Order No.	<a href="#">2715690000</a>	
GTIN (EAN)	4064675042082	
Qty.	1 ST	
Type	PJ CON TEXTILE COVER	Version
Order No.	<a href="#">2715670000</a>	
GTIN (EAN)	4064675042068	
Qty.	1 ST	
Type	PJ CON WASTE PAD	Version
Order No.	<a href="#">2715660000</a>	
GTIN (EAN)	4064675042051	
Qty.	1 ST	

## PRINTJET CONNECT

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	PJ CON WIFI STICK	Version
Order No.	<a href="#">2715680000</a>	
GTIN (EAN)	6955690002749	
Qty.	1 ST	

## M-Print® PRO



The M-Print® PRO printing and ordering software for markers and labels® is a professional Windows®-based solution for both printing and ordering Weidmüller labels and markers. This software allows you to optimise the process of identifying electrical equipment. You can design and order your marking materials easily, professionally and quickly: with text, frames, lines, graphics, bar codes, serial numbers and photos.

- Integrated product catalogue for all labels and markers, incl. images, link to the website and product data sheet
- Markers and labels can be designed on as many levels as required
- Customised formatting of individual text characters (RTF)
- Copy and paste texts and their formats
- Available in 20 languages supporting UNICODE
- Data entry in labels and spreadsheets, or directly in Microsoft Excel
- Creation of scales; numeric and alpha-numeric counters and sequences
- Extensive range of image formats (\*.bmp, \*.wmf, \*.png, \*.ico, \*.jpeg, \*.jpg, \*.tif, \*.gif)
- Image library including symbols used in electrical engineering
- Product-printer allocation options, e.g. ESG 9/20 to PrintJet; MultiMark on thermotransfer printer
- Online update service via the Internet
- Weidmueller Configurator (WMC) interface
- Import wizard for a number of file formats (\*.txt, \*.csv, \*.xml, etc.) for creating your own import scripts
- Transfer of data from CAE systems
- Permanent print preview: see what the printout will look like even at the design phase, WYSIWYG editing
- Supported output devices: All Weidmueller printers (e.g. PrintJet CONNECT, THM MultiMark, etc.) and standard printers with Microsoft Windows® driver
- Optimal and fast adaptation of output devices
- Multi-level structuring of markers and labels

## General ordering data

Type	M-PRINT PRO	Version
Order No.	<a href="#">1905490000</a>	Software for markings, Software, Windows 10, Windows 11, Printer
GTIN (EAN)	4032248526291	software
Qty.	1 ST	