

VP HEX M25 PA6 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|--|
| Version | Blanking plugs, in closed state, M 25 x 1.5, 15 mm, Polyamide 6 (PA 6) |
| Order No. | 2715760000 |
| Type | VP HEX M25 PA6 GY |
| GTIN (EAN) | 4050118805420 |
| Qty. | 25 items |

VP HEX M25 PA6 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|----------------------|--------|----------------------|-------------|
| Height | 5.8 mm | Height (inches) | 0.2283 inch |
| Width | 28 mm | Width (inches) | 1.1024 inch |
| Length | 15 mm | Length (inches) | 0.5906 inch |
| Diameter | 32 mm | Wall thickness, min. | 0.5 mm |
| Wall thickness, max. | 14 mm | Net weight | 5.67 g |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -20 °C...100 °C |
|-----------------------|-----------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|-----------------------------------|-----------------------------|-----------------------------------|------------------------------|
| Tightening torque | 2.5 Nm | UL 94 flammability rating | V-2 |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -20 °C |
| Pitch of thread | 1.5 mm | Halogen | No |
| Standards | in accordance with UL94 V-2 | Protection degree | IP65, IP68 - 5 bar (30 min.) |
| Cable gland | metric | Basic material | Polyamide 6 (PA 6) |
| Diameter of sealing ring | 25.00 mm | External thread | M 25 x 1.5 |
| Length of thread | 15 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000451 | ETIM 9.0 | EC000451 |
| ETIM 10.0 | EC000451 | ECLASS 14.0 | 27-14-08-05 |
| ECLASS 15.0 | 27-14-08-05 | | |