

HDC 06B AF WM COVER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Our flange-mounted housings made of plastic have a built-in cable gland and a screw interlock. They seal directly onto the panel wall and can therefore be used without an attachment housing. The housings are impressive with their low weight and optimal protection against contamination, water and vibrations.

General ordering data

Version	HDC enclosures, Installation size: 3, Protection degree: IP66, in plugged condition, Cover for lower part of housing, Screw
Order No.	2716810000
Type	HDC 06B AF WM COVER
GTIN (EAN)	4050118803686
Qty.	1 items

HDC 06B AF WM COVER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223801

Dimensions and weights

Depth	55 mm	Depth (inches)	2.1654 inch
Height	39.5 mm	Height (inches)	1.5551 inch
Width	100.5 mm	Width (inches)	3.9567 inch
Length	100.5 mm	Length (inches)	3.9567 inch
Net weight	4.6 g		

Temperatures

Ambient temperature -20 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Dimensions

Cable entry No

General data

Tightening torque	3 Nm	UL 94 flammability rating	V-0
Housing main material	PA	Protection degree	IP66, in plugged condition
EMC housings	No	Material of locking element	Stainless steel, rust-proof

Version

Top part/bottom part/lid	Cover	Cover	with cover
Tightening torque	3 Nm	Number of cable entry sideways	0
Design of housing	Cover for lower part of housing	Design of locking system	Screw
Installation size	3	Cable entry	No
Type	Cover	Sealing	NBR
Colour (RAL)	RAL 7035	BG	3
Suitable for ModuPlug®	Yes		

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		