

**HDC 10B AF WM COVER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Our flange-mounted housings made of plastic have a built-in cable gland and a screw interlock. They seal directly onto the panel wall and can therefore be used without an attachment housing. The housings are impressive with their low weight and optimal protection against contamination, water and vibrations.

**General ordering data**

|            |   |
|------------|---|
| Version    | HDC enclosures, Installation size: 4, Protection degree: IP66, in plugged condition, Cover for lower part of housing, Screw |
| Order No.  | <a href="#">2716820000</a>  |
| Type       | HDC 10B AF WM COVER   |
| GTIN (EAN) | 4050118803693   |
| Qty.       | 1 items   |

**HDC 10B AF WM COVER**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate No. (cURus) | E223801                    |

**Dimensions and weights**

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 55 mm    | Depth (inches)  | 2.1654 inch |
| Height     | 39.5 mm  | Height (inches) | 1.5551 inch |
| Width      | 102.5 mm | Width (inches)  | 4.0354 inch |
| Length     | 102.5 mm | Length (inches) | 4.0354 inch |
| Net weight | 42.24 g  |                 |             |

**Temperatures**

|                     |                 |
|---------------------|-----------------|
| Ambient temperature | -20 °C...100 °C |
|---------------------|-----------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Dimensions**

|             |    |
|-------------|----|
| Cable entry | No |
|-------------|----|

**General data**

|                           |     |                   |                            |
|---------------------------|-----|-------------------|----------------------------|
| UL 94 flammability rating | V-0 | Protection degree | IP66, in plugged condition |
|---------------------------|-----|-------------------|----------------------------|

**Version**

|                          |                                 |                                |            |
|--------------------------|---------------------------------|--------------------------------|------------|
| Top part/bottom part/lid | Cover                           | Cover                          | with cover |
| Tightening torque        | 3 Nm                            | Number of cable entry sideways | 0          |
| Design of housing        | Cover for lower part of housing | Design of locking system       | Screw      |
| Installation size        | 4                               | Cable entry                    | No         |
| Type                     | Cover                           | Sealing                        | NBR        |
| Colour (RAL)             | RAL 7035                        | BG                             | 4          |
| Suitable for ModuPlug®   | Yes                             |                                |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ETIM 10.0   | EC000437    | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 |             |             |