

IE-C5DE4UP0075PSSXXX-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Dragline cable, M8 P-code - IP67 straight socket, Open, Cat. 5e, PUR, 7.5 m
Order No.	2717740075
Type	IE-C5DE4UP0075PSSXXX-E
GTIN (EAN)	4050118778830
Qty.	1 items

IE-C5DE4UP0075PSSXXX-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Length	7.5 m	Length (inches)	295.2756 inch
Net weight	466 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...80 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Technical specifications for cable

Sheathing colour	black	Resistance to oils	in accordance with IEC 60811:404
Suitable for cable carriers	No	Number of wires	4
Shielded	Yes	Halogen	halogen-free, according to IEC 60754
Insulation	Polyolefin	Bending cycles	2 Mio
Resistance to spread of flame	Yes	Sheath material	PUR
Test voltage: wire-wire-shield	1 kV DC, 1 min, 1000 Veff, 50 Hz, 1 min	Colour coding	white, yellow, blue, orange
Temperature range, stationary	-40...80 °C	Temperature range, moving	-30...70 °C
Number of poles	4		

General technical data

Protection degree IP67

Plug, left

Plug left M8, P-coded, IP67, female contact, straight, plug, Plastic, shielded

Plug, right

Plug right free conductor end

Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

Drawings

Wiring

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4