


## IE-C5DE4UP0075PCSXXX-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

|            |  |
|------------|--|
| Version    | Dragline cable, M8 P-code - IP67 straight pin, Open, Cat. 5e, PUR, 7.5 m |
| Order No.  | <a href="#">2717750075</a>   |
| Type       | IE-C5DE4UP0075PCSXXX-E   |
| GTIN (EAN) | 4050118780024  |
| Qty.       | 1 items  |

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |       |                 |               |
|------------|-------|-----------------|---------------|
| Length     | 7.5 m | Length (inches) | 295.2756 inch |
| Net weight | 510 g |                 |               |

**Temperatures**

|                          |                       |                |
|--------------------------|-----------------------|----------------|
| Storage temperature      | Operating temperature | -40 °C...80 °C |
| Installation temperature |                       |                |

**Environmental Product Compliance**

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant                            |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 67cf1078-beca-4687-860b-dc475a6ec24a |

**Technical specifications for cable**

|                                |   |                           |                                      |
|--------------------------------|---|---------------------------|--------------------------------------|
| Sheathing colour               | black                                   | Resistance to oils        | in accordance with IEC 60811:404     |
| Suitable for cable carriers    | No                                      | Number of wires           | 4                                    |
| Shielded                       | Yes                                     | Halogen                   | halogen-free, according to IEC 60754 |
| Insulation                     | Polyolefin                              | Bending cycles            | 2 Mio                                |
| Resistance to spread of flame  | Yes                                     | Sheath material           | PUR                                  |
| Test voltage: wire-wire-shield | 1 kV DC, 1 min, 1000 Veff, 50 Hz, 1 min | Colour coding             | white, yellow, blue, orange          |
| Temperature range, stationary  | -40...80 °C                             | Temperature range, moving | -30...70 °C                          |
| Number of poles                | 4                                       |                           |                                      |

**General technical data**

Protection degree IP67

**Plug, left**

Plug left M8, P-coded, IP67, male contact, straight, plug, Plastic, shielded

**Plug, right**

Plug right free conductor end

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 |             |             |

**Drawings**

**Wiring**

| M12 |        | M12 |
|-----|--------|-----|
| 1   | yellow | 1   |
| 2   | white  | 2   |
| 3   | orange | 3   |
| 4   | blue   | 4   |