

## IE-C5DE4UP0100PCSXXX-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Dragline cable, M8 P-code - IP67 straight pin, Open, Cat. 5e, PUR, 10 m
Order No.	<a href="#">2717750100</a>
Type	IE-C5DE4UP0100PCSXXX-E
GTIN (EAN)	4050118780031
Qty.	1 items

**IE-C5DE4UP0100PCSXXX-E**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Length	10 m	Length (inches)	393.7008 inch
Net weight	900 g		

**Temperatures**

Storage temperature	Operating temperature	-40 °C...80 °C
Installation temperature		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

**Technical specifications for cable**

Sheathing colour	black	Resistance to oils	in accordance with IEC 60811:404
Suitable for cable carriers	No	Number of wires	4
Shielded	Yes	Halogen	halogen-free, according to IEC 60754
Insulation	Polyolefin	Bending cycles	2 Mio
Resistance to spread of flame	Yes	Sheath material	PUR
Test voltage: wire-wire-shield	1 kV DC, 1 min, 1000 Veff, 50 Hz, 1 min	Colour coding	white, yellow, blue, orange
Temperature range, stationary	-40...80 °C	Temperature range, moving	-30...70 °C
Number of poles	4		

**General technical data**

Protection degree IP67

**Plug, left**

Plug left M8, P-coded, IP67, male contact, straight, plug, Plastic, shielded

**Plug, right**

Plug right free conductor end

**Classifications**

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

**Drawings**

**Wiring**

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4