

IE-C5DE4UP0075PCAPSA-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|--|
| Version | Dragline cable, M8 P-code - IP67 angeled pin, M8 P-code - IP67 angeled socket, Cat. 5e, PUR, 7.5 m |
| Order No. | 2717810075 |
| Type | IE-C5DE4UP0075PCAPSA-E |
| GTIN (EAN) | 4050118779882 |
| Qty. | 1 items |

IE-C5DE4UP0075PCAPSA-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|-------|-----------------|---------------|
| Length | 7.5 m | Length (inches) | 295.2756 inch |
| Net weight | 472 g | | |

Temperatures

| | | |
|--------------------------|-----------------------|----------------|
| Storage temperature | Operating temperature | -40 °C...80 °C |
| Installation temperature | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Technical specifications for cable

| | | | |
|--------------------------------|---|---------------------------|--------------------------------------|
| Sheathing colour | black | Resistance to oils | in accordance with IEC 60811:404 |
| Suitable for cable carriers | No | Number of wires | 4 |
| Shielded | Yes | Halogen | halogen-free, according to IEC 60754 |
| Insulation | Polyolefin | Bending cycles | 2 Mio |
| Resistance to spread of flame | Yes | Sheath material | PUR |
| Test voltage: wire-wire-shield | 1 kV DC, 1 min, 1000 Veff, 50 Hz, 1 min | Colour coding | white, yellow, blue, orange |
| Temperature range, stationary | -40...80 °C | Temperature range, moving | -30...70 °C |
| Number of poles | 4 | | |

General technical data

Protection degree IP67

Plug, left

Plug left M8, P-coded, IP67, male contact, angled 90°, plug, Plastic, shielded

Plug, right

Plug right M8, P-coded, IP67, female contact, angled 90°, plug, Plastic, shielded

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 | | |

Drawings

Wiring

| M12 | | M12 |
|-----|--------|-----|
| 1 | yellow | 1 |
| 2 | white | 2 |
| 3 | orange | 3 |
| 4 | blue | 4 |