

## KCMA-8-250-5A-1.5VA1

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Current transformers for retrofitting

#### Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

### General ordering data

Version	Primary current: 250 A, Secondary current max.: 5 A, Load: 1.5 VA, Tolerance class: 1, Split-core current transformer
Order No.	<a href="#">2728090000</a>
Type	KCMA-8-250-5A-1.5VA1
GTIN (EAN)	4050118813685
Qty.	1 items
Manufacturer	MBS AG

**KCMA-8-250-5A-1.5VA1**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 1259.28 g

**Temperatures**

Storage temperature Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Dimensions of live conductors**

Type of conductor	Insulated conductor only	Round conductor	80.00 mm
Rail	80 x 120 mm		

**Electrical attributes**

Tolerance class	1	Secondary current	0...5 A
Load	1.5 VA	Primary current	250 A

**Technical properties**

Protection degree IP20 Nominal frequency 50 Hz

**Insulation coordination**

Tolerance class 1

**Classifications**

ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

KCMA-8-250-5A-1.5VA1

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

[www.weidmueller.com](http://www.weidmueller.com)

