

IE-BS-M12X-S-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	2731010000
Type	IE-BS-M12X-S-C
GTIN (EAN)	4050118809282
Qty.	1 items

IE-BS-M12X-S-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Wall thickness, max.	4.5 mm	Net weight	1.7 g
----------------------	--------	------------	-------

Temperatures

Storage temperature	Operating temperature	-40 °C...85 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Technical data customisable plug-in connectors

Number of poles	8	Coding	X-coded
Contact surface	Au (Gold)	Housing main material	Brass, Copper-tin-zinc alloy
Insulation resistance	≥ 100 MΩ	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Contact material	CuSn	Nominal voltage	50 V
Protection degree	IP67 plugged	Plugging cycles	≥ 100

General Info

Number of poles	8	Connection 1	M12
Connection 2	M12	Description of article	Coupling
Composition	M12 socket to M12 socket	Wiring	8-core
UL 94 flammability rating	UL 94, V-0	Housing main material	Brass, Copper-tin-zinc alloy
Category	Cat.6A / Class EA (ISO/IEC 11801 2010)	Connection thread	M12 / M12
Contact material	CuSn	Contact surface	Au (Gold)
Contact holder materials	PA UL 94 V0	Shielding material	Zinc diecast, tin plated
Shielding	Yes	Protection degree	IP67 plugged
Plugging cycles	≥ 100		

Electrical properties

Contact resistance	≤ 5 mΩ	
Dielectric strength, contact / shield	≥ 500 V DC	
Dielectric strength, contact / contact	≥ 500 V DC	
Insulation resistance	≥ 100 MΩ	
Nominal voltage	50 V	
Current-carrying capacity	Current-carrying capacity	0.5 A
	Temperature	40 °C
PoE / PoE+	conforming to IEEE 802.3at	
Operational voltage range	50 V AC, 60 V DC	

IE-BS-M12X-S-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Standards

Connector standard	IEC 61076-2-109	UL standard for communication accessories	UL 1863
IP protection classes	IEC 60529		


General technical specifications

Number of poles	8	Coding	X-coded
Connection thread	M12 / M12	Contact surface	Au (Gold)
UL 94 flammability rating	UL 94, V-0	Housing main material	Brass, Copper-tin-zinc alloy
Insulation resistance	≥ 100 MΩ	Contact material	CuSn
Nominal voltage	50 V	Protection degree	IP67 plugged
Plugging cycles	≥ 100		


Classifications

ETIM 8.0	EC000313	ETIM 9.0	EC000313
ETIM 10.0	EC000313	ECLASS 14.0	27-44-03-20
ECLASS 15.0	27-44-03-20		

Dimensional drawing




Installation cut-out




A through hole without twist protection

Installation cut-out




A through hole with twist protection

Installation cut-out



A threaded hole

Installation cut-out



B through hole with twist protection

IE-BS-M12X-S-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SET	Version	
Order No.	1910000000		Cable gland tool for M8, M12 lines and connectors
GTIN (EAN)	4032248436842		
Qty.	1 ST		

Screwty® cable gland tool with torque function



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SET -DM	Version	
Order No.	1920000000		Cable gland tool for M8, M12 lines and connectors
GTIN (EAN)	4032248436859		
Qty.	1 ST		

IE-BS-M12X-S-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY- M12 F	Version	
Order No.	1900020000		Cable gland tool for M12 connectors
GTIN (EAN)	4032248375851		
Qty.	1 ST		

Screwty® cable gland tool with torque function



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY-M12 F-DM	Version	
Order No.	1900021000		Cable gland tool for M12 connectors
GTIN (EAN)	4032248436828		
Qty.	1 ST		