

BIT E6,3 0,4X2,5X70

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Version	Screwdriver insert, Blade width (B): 2.5 mm, Blade length: 70 mm, Blade thickness (A): 0.4 mm
Order No.	2748900000
Type	BIT E6,3 0,4X2,5X70
GTIN (EAN)	4050118894776
Qty.	5 items

BIT E6,3 0,4X2,5X70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Width	70 mm	Width (inches)	2.7559 inch
Net weight	8.27 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Bit with slotted blade 0.4 x 2.5 x 70
------------------------	---------------------------------------

Screwing tools

Blade width (B)	2.5 mm	Blade thickness (A)	0.4 mm
Form	E 6.3 DIN 3126, Slotted	Blade length	70 mm

Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-04
ECLASS 15.0	21-04-42-04		