

## BIT E6,3 PH2X70

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits are Phillips-Recessed type PH/DIN 5260.  
1/4" drive, E6.3 DIN 3126

### General ordering data

Version	Screwdriver insert, Blade width (B): 2 mm, Blade length: 70 mm, Blade thickness (A): 2 mm, Blade size, crosshead: 2
Order No.	<a href="#">2748990000</a>
Type	BIT E6,3 PH2X70
GTIN (EAN)	4050118895186
Qty.	5 items

## BIT E6,3 PH2X70

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Width	70 mm	Width (inches)	2.7559 inch
Net weight	14 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Description of article	Bit with crosshead, Phillips size 2
------------------------	-------------------------------------

### Screwing tools

Blade width (B)	2 mm	Blade thickness (A)	2 mm
Form	E 6.3 DIN 3126, Crosshead	Size	2
Blade length	70 mm	Blade size, crosshead	2

### Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-03
ECLASS 15.0	21-04-42-03		