

SDIL 0,5X3,0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Blade width (B): 3 mm, 100 mm, Blade thickness (A): 0.5 mm
Order No.	2749130000
Type	SDIL 0,5X3,0X100
GTIN (EAN)	4050118895438
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-02-28T00:00:00+01:00

SDIL 0,5X3,0X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

Approvals


Dimensions and weights

Width	185 mm	Width (inches)	7.2835 inch
Diameter	3 mm	Net weight	31.68 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.5x3.0x100	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	3 mm	Blade thickness (A)	0.5 mm
Form	Slotted	Blade length	100 mm

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		