

SDIL 0,6X3,5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Blade width (B): 3.5 mm, 100 mm, Blade thickness (A): 0.6 mm
Order No.	2749140000
Type	SDIL 0,6X3,5X100
GTIN (EAN)	4050118895445
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-28T00:00:00+01:00

SDIL 0,6X3,5X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Width	190 mm	Width (inches)	7.4803 inch
Diameter	3.5 mm	Net weight	34.32 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.6x3.5x100	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	3.5 mm	Blade thickness (A)	0.6 mm
Form	Slotted	Blade length	100 mm

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		