

SDIKL PH1X80**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
Order No.	2749180000
Type	SDIKL PH1X80
GTIN (EAN)	4050118895483
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-02-28T00:00:00+01:00

SDIKL PH1X80

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

Approvals

**Dimensions and weights**

Width	180 mm	Width (inches)	7.0866 inch
Net weight	70 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Version	straight
---------	----------

Screwing tools

Blade width (B)	1 mm	Form	Philips
Size	1	Blade length	80 mm
Blade size, crosshead	1		

Classifications

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		