

## SDS 0.4X2.5X75

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-Top tip, SoftFinish grip

### General ordering data

Version	Screwdriver, Blade width (B): 2.5 mm, Blade length: 75 mm, Blade thickness (A): 0.4 mm
Order No.	<a href="#">2749320000</a>
Type	SDS 0.4X2.5X75
GTIN (EAN)	4050118895544
Qty.	1 items

**SDS 0.4X2.5X75**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	180 mm	Length (inches)	7.0866 inch
Diameter	2.5 mm	Net weight	29.92 g

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Technical data**

Description of article	Screwdriver with slotted bit, 0.4 x 2.5	Version	straight
------------------------	---	---------	----------

**Screwing tools**

Blade width (B)	2.5 mm	Blade thickness (A)	0.4 mm
Form	Slotted	Blade length	75 mm
Blade type	A		

**Classifications**

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		