

SDS 0.8X4.0X100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	2749360000
Type	SDS 0.8X4.0X100
GTIN (EAN)	4050118895582
Qty.	1 items

SDS 0.8X4.0X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	210 mm	Width (inches)	8.2677 inch
Length	205 mm	Length (inches)	8.0709 inch
Diameter	4 mm	Net weight	44 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	Insulated screwdriver with slotted bit 0.8x4	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	4 mm	Blade thickness (A)	0.8 mm
Form	Slotted	Blade length	100 mm
Blade type	A		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		