

SDS 1.2X6.5X150

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 6.5 mm, Blade length: 150 mm, Blade thickness (A): 1.2 mm
Order No.	2749390000
Type	SDS 1.2X6.5X150
GTIN (EAN)	4050118895612
Qty.	1 items

SDS 1.2X6.5X150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	268 mm	Width (inches)	10.5512 inch
Length	265 mm	Length (inches)	10.433 inch
Diameter	6.5 mm	Net weight	100 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	Screwdriver with slotted bit 1.2x6.5	Version	straight
------------------------	--------------------------------------	---------	----------

Screwing tools

Blade width (B)	6.5 mm	Blade thickness (A)	1.2 mm
Form	Slotted	Blade length	150 mm
Blade type	A		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		