

SDIS SLIM 0.8X4.0X100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | |
|------------|---|
| Version | Mounting tool, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm |
| Order No. | 2749620000 |
| Type | SDIS SLIM 0.8X4.0X100 |
| GTIN (EAN) | 4050118896367 |
| Qty. | 1 items |

SDIS SLIM 0.8X4.0X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

| | | | |
|----------|--------|-----------------|-------------|
| Length | 205 mm | Length (inches) | 8.0709 inch |
| Diameter | 4 mm | Net weight | 38.72 g |

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | VDE-insulated screwdriver with slotted blade 0.8x4.0x100, SlimLine | Version | straight |
|------------------------|--|---------|----------|

Screwing tools

| | | | |
|-----------------|---------|---------------------|--------|
| Blade width (B) | 4 mm | Blade thickness (A) | 0.8 mm |
| Form | Slotted | Blade length | 100 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000158 | ETIM 9.0 | EC000158 |
| ETIM 10.0 | EC000158 | ECLASS 14.0 | 21-04-04-07 |
| ECLASS 15.0 | 21-04-04-07 | | |