

## SDIS SLIM 0.8X4.0X100

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

### General ordering data

Version	Mounting tool, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	<a href="#">2749620000</a>
Type	SDIS SLIM 0.8X4.0X100
GTIN (EAN)	4050118896367
Qty.	1 items

**SDIS SLIM 0.8X4.0X100**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Length	205 mm	Length (inches)	8.0709 inch
Diameter	4 mm	Net weight	38.72 g

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	VDE-insulated screwdriver with slotted blade 0.8x4.0x100, SlimLine	Version	straight
------------------------	--	---------	----------

**Screwing tools**

Blade width (B)	4 mm	Blade thickness (A)	0.8 mm
Form	Slotted	Blade length	100 mm

**Classifications**

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		