

SDIS 0.4X2.0X60

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm
Order No.	2749780000
Type	SDIS 0.4X2.0X60
GTIN (EAN)	4050118896527
Qty.	1 items

Technical data

Approvals

Approvals



Dimensions and weights

Width	164 mm	Width (inches)	6.4567 inch
Length	165 mm	Length (inches)	6.4961 inch
Diameter	2 mm	Net weight	29.04 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.4 x 2.0 x 60	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade width (B)	2 mm	Blade thickness (A)	0.4 mm
Form	Slotted	Blade length	60 mm
Blade type	A		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		