

SDIS 0.4X2.5X75

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2.5 mm, Blade length: 75 mm, Blade thickness (A): 0.4 mm
Order No.	2749790000
Type	SDIS 0.4X2.5X75
GTIN (EAN)	4050118896534
Qty.	1 items

SDIS 0.4X2.5X75

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	180 mm	Length (inches)	7.0866 inch
Diameter	2.5 mm	Net weight	32 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.4x2.5x75	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade width (B)	2.5 mm	Blade thickness (A)	0.4 mm
Form	Slotted	Blade length	75 mm
Blade type	A		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		