

## SDIS 1.0X4.5X125

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

### General ordering data

Version	Screwdriver, Blade width (B): 4.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm
Order No.	<a href="#">2749830000</a>
Type	SDIS 1.0X4.5X125
GTIN (EAN)	4050118897036
Qty.	1 items

**SDIS 1.0X4.5X125**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Length	230 mm	Length (inches)	9.0551 inch
Diameter	4.5 mm	Net weight	110 g

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Technical data**

Description of article	VDE-insulated screwdriver with slotted blade 1.0x4.5x125	Version	straight
------------------------	--	---------	----------

**Screwing tools**

Blade width (B)	4.5 mm	Blade thickness (A)	1 mm
Form	Slotted	Blade length	125 mm
Blade type	B		

**Classifications**

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		