Data sheet

SDIS 1.0X4.5X175

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4.5 mm, Blade length: 175 mm, Blade thickness (A): 1 mm
Order No.	2749840000
Type	SDIS 1.0X4.5X175
GTIN (EAN)	4050118897043
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2025-12-31T00:00:00+01:00

Data sheet

SDIS 1.0X4.5X175

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	

Dimensions and weights

Length	280 mm	Length (inches)	11.0236 inch
Diameter	4.5 mm	Net weight	64 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 1.0 x 4.5 x 175	Version	straight

Screwing tools

Blade width (B)	4.5 mm	Blade thickness (A)	1 mm
Form	Slotted	Blade length	175 mm
Blade type	B		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		