

SDIS 1.2X8.0X175

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

| | |
|------------|---|
| Version | Screwdriver, Blade width (B): 8 mm, Blade length: 175 mm, Blade thickness (A): 1.6 mm |
| Order No. | 2749870000 |
| Type | SDIS 1.2X8.0X175 |
| GTIN (EAN) | 4050118897074 |
| Qty. | 1 items |

Technical data

Approvals

Approvals



Dimensions and weights

| | | | |
|----------|--------|-----------------|--------------|
| Length | 290 mm | Length (inches) | 11.4173 inch |
| Diameter | 8 mm | Net weight | 132 g |

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | VDE-insulated screwdriver with slotted blade 1.6x8.0x175 | Version | straight |
|------------------------|--|---------|----------|

Screwing tools

| | | | |
|-----------------|---------|---------------------|--------|
| Blade width (B) | 8 mm | Blade thickness (A) | 1.6 mm |
| Form | Slotted | Blade length | 175 mm |
| Blade type | B | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000158 | ETIM 9.0 | EC000158 |
| ETIM 10.0 | EC000158 | ECLASS 14.0 | 21-04-04-07 |
| ECLASS 15.0 | 21-04-04-07 | | |