

SDIS 1.2X8.0X175

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 8 mm, Blade length: 175 mm, Blade thickness (A): 1.6 mm
Order No.	2749870000
Type	SDIS 1.2X8.0X175
GTIN (EAN)	4050118897074
Qty.	1 items

Technical data

Approvals

Approvals



Dimensions and weights

Length	290 mm	Length (inches)	11.4173 inch
Diameter	8 mm	Net weight	132 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 1.6x8.0x175	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	8 mm	Blade thickness (A)	1.6 mm
Form	Slotted	Blade length	175 mm
Blade type	B		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		