

SDIK PH1 X 80



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
Order No.	2749890000
Type	SDIK PH1 X 80
GTIN (EAN)	4050118897098
Qty.	1 items

Technical data

Approvals

Approvals



Dimensions and weights

Width	185 mm	Width (inches)	7.2835 inch
Net weight	50 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated crosshead screwdriver, Phillips size 1	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	1 mm	Form	Phillips, round
Size	1	Blade length	80 mm
Blade size, crosshead	1		

Classifications

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		