

SDIK PH2 X 100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
Order No.	2749900000
Type	SDIK PH2 X 100
GTIN (EAN)	4050118897203
Qty.	1 items

SDIK PH2 X 100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Width	220 mm	Width (inches)	8.6614 inch
Net weight	95 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated crosshead screwdriver, Phillips size 2	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	2 mm	Form	Phillips, round
Size	2	Blade length	100 mm
Blade size, crosshead	2		

Classifications

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		