

## SDIK PZ1 X 80



VDE insulated crosshead screwdriver type Pozidriv SDIK PZ DIN 7438, ISO 8764/2-PZ, output to ISO 8764-PZ, SoftFinish grip

### General ordering data

Version	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
Order No.	<a href="#">2749920000</a>
Type	SDIK PZ1 X 80
GTIN (EAN)	4050118897227
Qty.	1 items

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Width	185 mm	Width (inches)	7.2835 inch
Net weight	46 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	VDE-insulated crosshead screwdriver, Pozidrive size 1	Version	straight
------------------------	---	---------	----------

**Screwing tools**

Blade width (B)	1 mm	Form	Pozidrive, round
Size	1	Blade length	80 mm
Blade size, crosshead	1		

**Classifications**

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		