

## SDIK PZ2 X 100

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



VDE insulated crosshead screwdriver type Pozidriv SDIK PZ DIN 7438, ISO 8764/2-PZ, output to ISO 8764-PZ, SoftFinish grip

### General ordering data

Version	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
Order No.	<a href="#">2749930000</a>
Type	SDIK PZ2 X 100
GTIN (EAN)	4050118897234
Qty.	1 items

**SDIK PZ2 X 100**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Width	215 mm	Width (inches)	8.4645 inch
Net weight	82.72 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Technical data**

Description of article	VDE-insulated crosshead screwdriver, Pozidrive size 2	Version	straight
------------------------	-------------------------------------------------------	---------	----------

**Screwing tools**

Blade width (B)	2 mm	Form	Pozidrive, round
Size	2	Blade length	100 mm
Blade size, crosshead	2		

**Classifications**

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		