

SDIK PZ2 X 100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



VDE insulated crosshead screwdriver type Pozidriv SDIK PZ DIN 7438, ISO 8764/2-PZ, output to ISO 8764-PZ, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
Order No.	2749930000
Type	SDIK PZ2 X 100
GTIN (EAN)	4050118897234
Qty.	1 items

Technical data

Approvals

Approvals



Dimensions and weights

Width	215 mm	Width (inches)	8.4645 inch
Net weight	82.72 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	VDE-insulated crosshead screwdriver, Pozidrive size 2	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade width (B)	2 mm	Form	Pozidrive, round
Size	2	Blade length	100 mm
Blade size, crosshead	2		

Classifications

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		