

SDIPM PZ1 X 80**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
Order No.	2749940000
Type	SDIPM PZ1 X 80
GTIN (EAN)	4050118897241
Qty.	1 items

SDIPM PZ1 X 80

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Width	185 mm	Width (inches)	7.2835 inch
Net weight	40.48 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated crosshead screwdriver, Pozidrive size 1	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade width (B)	1 mm	Form	Crosshead, round
Size	1	Blade length	80 mm
Blade size, crosshead	1		

Classifications

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		