

## SDIPM PH1 X 80

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

### General ordering data

Version	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
Order No.	<a href="#">2749960000</a>
Type	SDIPM PH1 X 80
GTIN (EAN)	4050118897265
Qty.	1 items

**SDIPM PH1 X 80**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Width	185 mm	Width (inches)	7.2835 inch
Net weight	40.48 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	SlimLine, VDE-insulated crosshead screwdriver, Phillips size 1	Version	straight
------------------------	----------------------------------------------------------------	---------	----------

**Screwing tools**

Blade width (B)	1 mm	Form	Crosshead, Philips, round
Size	1	Blade length	80 mm
Blade size, crosshead	1		

**Classifications**

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		