

**SDIPM PH2 X 100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**General ordering data**

Version	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
Order No.	<a href="#">2749970000</a>
Type	SDIPM PH2 X 100
GTIN (EAN)	4050118897272
Qty.	1 items

**SDIPM PH2 X 100**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Width	215 mm	Width (inches)	8.4645 inch
Net weight	81.84 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	VDE-insulated crosshead screwdriver, Phillips size 2	Version	straight
------------------------	--	---------	----------

**Screwing tools**

Blade width (B)	2 mm	Form	Crosshead, Philips, round
Size	2	Blade length	100 mm
Blade size, crosshead	2		

**Classifications**

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		