

SDIZ 0.6X3.5X100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	2749980000
Type	SDIZ 0.6X3.5X100
GTIN (EAN)	4050118897289
Qty.	1 items

SDIZ 0.6X3.5X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Width	205 mm	Width (inches)	8.0709 inch
Net weight	40 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with pilot tip 0.6 x 3.5 x 100
------------------------	--

Screwing tools

Blade thickness (A)	0.6 mm	Form	Slotted
Blade length	100 mm	Blade type	A

Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		