

## SDIZ 0.8X4.0X100

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

### General ordering data

Version	Screwdriver, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	<a href="#">2749990000</a>
Type	SDIZ 0.8X4.0X100
GTIN (EAN)	4050118897296
Qty.	1 items

**SDIZ 0.8X4.0X100**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Width	210 mm	Width (inches)	8.2677 inch
Net weight	39.6 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	VDE-insulated screwdriver with pilot tip 0.8 x 4.0 x 100
------------------------	--

**Screwing tools**

Blade thickness (A)	0.8 mm	Form	Slotted
Blade length	100 mm		

**Classifications**

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		