



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Mounting tool, Blade width (B): 2 mm, Blade length: 100 mm, Blade thickness (A): 2 mm
Order No.	2750030000
Type	SDIR 2 X 100
GTIN (EAN)	4050118897517
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31T00:00:00+01:00

Technical data**Approvals**

Approvals

**Dimensions and weights**

Length	215 mm	Length (inches)	8.4645 inch
Diameter	2 mm	Net weight	82.72 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Version	straight
---------	----------

Screwing tools

Blade width (B)	2 mm	Blade thickness (A)	2 mm
Form	Square	Size	#2
Blade length	100 mm		

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		