

## SD EL 0.4X2.0X60 PICO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-Top tip, SoftFinish grip

### General ordering data

Version	Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm
Order No.	<a href="#">2750070000</a>
Type	SD EL 0.4X2.0X60 PICO
GTIN (EAN)	4050118897555
Qty.	1 items

**SD EL 0.4X2.0X60 PICO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	160 mm	Length (inches)	6.2992 inch
Diameter	2 mm	Net weight	11.44 g

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	Screwdriver with slotted bit, 0.4 x 2	Version	straight
------------------------	---------------------------------------	---------	----------

**Screwing tools**

Blade width (B)	2 mm	Blade thickness (A)	0.4 mm
Form	Slotted	Blade length	60 mm

**Classifications**

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		