

SD EL 0.5X3.0X75 PICO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 3 mm, Blade length: 75 mm, Blade thickness (A): 0.5 mm
Order No.	2750090000
Type	SD EL 0.5X3.0X75 PICO
GTIN (EAN)	4050118897579
Qty.	1 items

SD EL 0.5X3.0X75 PICO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	175 mm	Length (inches)	6.8898 inch
Diameter	3 mm	Net weight	13.2 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Screwdriver with slotted bit, 0.5 x 3	Version	straight
------------------------	---------------------------------------	---------	----------

Screwing tools

Blade width (B)	3 mm	Blade thickness (A)	0.5 mm
Form	Slotted	Blade length	75 mm

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		