

SD EL 0,6X3,5X100 PICO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	275010000
Type	SD EL 0,6X3,5X100 PICO
GTIN (EAN)	4050118897586
Qty.	1 items

SD EL 0,6X3,5X100 PICO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	200 mm	Length (inches)	7.874 inch
Diameter	3.5 mm	Net weight	18 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Screwdriver with slotted bit, 0.6 x 3.5	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade width (B)	3.5 mm	Blade thickness (A)	0.6 mm
Form	Slotted	Blade length	100 mm

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		