

SD EL 0.8X4.0X100 PICO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	2750110000
Type	SD EL 0.8X4.0X100 PICO
GTIN (EAN)	4050118897593
Qty.	1 items

SD EL 0.8X4.0X100 PICO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	200 mm	Length (inches)	7.874 inch
Diameter	4 mm	Net weight	20 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Version	straight
---------	----------

Screwing tools

Blade width (B)	4 mm	Blade thickness (A)	0.8 mm
Form	Slotted	Blade length	100 mm

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		